

Project:

Fixture Type:

Location:

Contact:

## **P710097-031** Stockbrace

Stockbrace Collection 1-Light Matte Black Clear Glass Modern Wall Light

Category: Wall Bracket Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Clear Glass Cone



Length: 4-3/4 in Extends: 5-1/2 in Height: 13-1/2 in H/CTR: 9-1/2 in

Clear Glass Cone Width: 4-1/2 in Height: 6-7/8 in

		Height: 6-7/8 in	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	Quantity: one 60 W max.	cULus Damp Location Listed
Swivel mounting strap for outlet box included	120 V	E26 base Porcelain Socket	1-year Limited Warranty
Can be mounted up or down			
Canopy covers a standard 4" recessed outlet box: 4.75" W., 7" ht., 0.87" depth			