

Project:

Fixture Type:

Location:

Contact:

## P710104-009 Carrick

Carrick Collection One-Light Brushed Nickel Summer Linen Shade Transitional Wall Light

Category: Wall Brackets Finish: Brushed Nickel (Plated) Construction: Steel Construction

Glass/Shade: Summer Linen Fabric Drum Shade, Etched Glass Diffuser



Length: 10 in Extends: 10-7/8 in Height: 11-3/4 in H/CTR: 7-7/8 in

Summer Linen Fabric Drum Shade

Width: 10 in Height: 5-1/2 in

Etched Glass Diffuser Width: 9-1/16 in Height: 0-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4"	Rotary On/Off switch on canopy	Incandescent: 60-watt MAX per socket	
recessed outlet box: 4.5" W., 7.87" ht., 0.75" depth	Hardwire only	LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	