

Project:			
Fixture Type:			
Location:			

# Pearl LED

Wall Mounted • Damp Location Listed PROGRESS LED

Contact:

### **Description:**

Pearl LED Collection Mid-Century Modern Satin Brass Etched Opal Glass Wall Bracket

### **Specifications:**

- · Etched Opal Glass Globe
- · Dimmable to 10% brightness (See Dimming Notes)
- · Canopy covers a standard 4" recessed outlet box: 5.75 in W., 12.0625 in ht., 1.25 in depth
- · Mounting backplate for outlet box included
- 6 in of wire supplied

#### **Performance:**

Number of Lights	1		
Input Power	6.5 W		
Input Voltage	120 V		
Input Frequency	60 Hz		
Lumens/LPW (Delivered)	450/69 (LM-79)		
CCT	3000 K		
CRI	90 CRI		
Life (hours)	50000 (L70/TM-21)		
EMI/RFI	FCC Title 47, Part 15, Class B		
Warranty	5-year Limited Warranty		
Labels	cETLus Damp Location Listed		
	Meets California Title 24 JA8-2019		

# P710105-012-30



## **Dimensions:**

Width: 5-3/4 in Extends: 5-7/16 in Height: 12-1/16 in H/CTR: 6-1/8 in

Etched Opal Glass Globe

Width: 4 in Height: 4 in



# Pearl LED

Wall Mounted • Damp Location Listed PROGRESS LED

### **Dimming Notes:**

P710105-012-30

P710105-012-30 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

### **Dimming Controls:**

Lutron NTEVL-300

Lutron DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.