

Project:

Fixture Type:

Location:

Contact:

Pearl LED

Wall Mounted • Damp Location Listed PROGRESS LED

Description:

Pearl LED Collection Mid-Century Modern Matte Black Etched Opal Glass Wall Bracket

Specifications:

- Etched Opal Glass Globe
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 5.75 in W., 12.0625 in ht., 1.25 in depth
- + Mounting backplate for outlet box included
- + 6 in of wire supplied

Performance:

Number of Lights	1
Input Power	6.5 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	412/63 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cETLus Damp Location Listed
	Meets California Title 24 JA8-2019

P710105-031-30



Dimensions:

Width: 5-3/4 in Extends: 5-7/16 in Height: 12-1/16 in H/CTR: 6-1/8 in

Etched Opal Glass Globe Width: 4 in Height: 4 in



Pearl LED

Wall Mounted • Damp Location Listed PROGRESS LED

P710105-031-30

Dimming Notes:

 $\mathsf{P710105}\text{-}031\text{-}30$ is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron NTEVL-300

Lutron DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.