

| Project:      |  |  |
|---------------|--|--|
| Fixture Type: |  |  |
| Location:     |  |  |
| Contact:      |  |  |

## **P710108-009** Saffert

Saffert Collection One-Light New Traditional Brushed Nickel Clear Glass Wall Light

Category: Wall Brackets Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Bowl



Width: 7-1/2 in Extends: 10-1/4 in Height: 24-1/2 in H/CTR: 8-5/8 in

Clear Glass Bowl Width: 7-1/2 in Height: 6-1/16 in

| MOUNTING   | ELECTRICAL                | LAMPING                       | ADDITIONAL INFORMATION     |
|--|---------------------------|-------------------------------|----------------------------|
| Wall mounted                                       | 6 inches of wire supplied | (1) Medium Base (E26) Socket  | cULus Damp Location Listed |
| Mounting plate for outlet box included             | 120 VAC                   | Lamp Type A19                 | 1-year Limited Warranty    |
|  |                           | Incandescent: 60-watt MAX per |                            |
| Fixture can be installed with glass                |                           | socket                        |                            |
| facing up or down                                  |                           | LED: 12.5-watt MAX per socket |                            |
| Canopy covers a standard 4"                        |                           | Fully dimmable with dimmable  |                            |
| recessed outlet box: 5" W., 8" ht.,<br>0.75" depth |                           | bulbs                         |                            |