

Project:		
Fixture Type:		
Location:		
Contact:		

P710109-009

Galloway

Category: Wall Brackets

Finish: Brushed Nickel (Plated) with Grey Washed Oak accent

Construction: Steel Construction



Width: 5-1/2 in Extends: 4-1/2 in Height: 18-1/8 in H/CTR: 9-1/16 in

		, - ,		
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION	
Wall mounted	6 inches of wire supplied	(1) Candelabra Base (E12) Socket	cETLus Damp Location Listed	
Mounting backplate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty	
		Incandescent: 60-watt MAX per		
Back Plate covers a standard 4"		socket		
recessed outlet box: 5.5" W., 18.12" ht., 0.75" depth		LED: 12.5-watt MAX per socket		
		Fully dimmable with dimmable bulbs		