



Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P710109-31M Galloway

Category: Wall Brackets
Finish: Matte Black (Painted) with Distressed White accent
Construction: Steel Construction



Width: 5-1/2 in
 Extends: 4-1/2 in
 Height: 18-1/8 in
 H/CTR: 9-1/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Candelabra Base (E12) Socket	cETLus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Back Plate covers a standard 4" recessed outlet box: 5.5" W., 18.12" ht., 0.75" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	