

Project:			
Fixture Type:			
Location:			
Contact:			

P710111-109

Parkhurst

Parkhurst Collection Two-Light Brushed Bronze Etched Glass New Traditional Wall Sconce

Category: Wall Sconce

Finish: Brushed Bronze (Plated) **Construction:** Steel Construction

Glass/Shade: Etched White Glass Curved Flat,



Width: 7.5 in Extends: 4 in Height: 12 in H/CTR: 6 in

Etched White Glass Curved Flat

Width: 3-3/16 in Height: 10-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Porcelain	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 7.5" W., 12" ht., 0.75" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	Americans With Disabilities Act (ADA) compliant
nt., 0.73 depth		Fully dimmable with dimmable bulbs	