PROGRESS LIGHTING

Project:

Fixture Type:

Location:

Contact:

P710111-31M Parkhurst

Parkhurst Collection Two-Light Matte Black Etched Glass New Traditional Wall Sconce

Category: Wall Sconce Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Etched White Glass Curved Flat,



Width: 7.5 in Extends: 4 in Height: 12 in H/CTR: 6 in

Etched White Glass Curved Flat Width: 3-3/16 in Height: 10-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Porcelain	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4"		Incandescent: 60-watt MAX per socket	Americans With Disabilities Act (ADA) compliant
recessed outlet box: 7.5" W., 12" ht., 0.75" depth		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	