

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P710112-109 Trimble

Trimble Collection One-Light Brushed Bronze Wall Bracket

Category: Wall Bracket

Finish: Brushed Bronze (Plated) with Matte Black accent

Construction: Steel Construction



Width: 8 in
Extends: 9-7/8 in
Height: 6 in (does not include bulb)
H/CTR: 2-5/8 in (bulb facing up)

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with bulb facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.81" ht., 5.12" depth		Fully dimmable with dimmable bulbs	