

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P710113-109 Trimble

Trimble Collection One-Light Brushed Nickel Wall Bracket

Category: Wall Bracket

Finish: Brushed Bronze (Plated)

Construction: Steel Construction



Width: 10 in
Extends: 21-7/8 in
Height: 10 in
H/CTR: 7 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 6.18" W., 4.75" ht., 0.81" depth	Switch Type: Push button	Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	