



Project:

Fixture Type:

Location:

Contact:

P710115-31M Cofield

Cofield Collection Two-Light Matte Black Transitional Wall Bracket

Category: Wall Brackets Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Clear Glass Cylindrical



Width: 22-1/2 in Extends: 5-5/8 in Height: 4-7/8 in H/CTR: 11-1/4 in (glass facing up)

Clear Glass Cylindrical Width: 4 in Height: 8-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall horizontal or vertical	6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.87" W., 0.87" ht., 4.87" depth		Fully dimmable with dimmable bulbs	