

Project:			
Fixture Type:			
Location:			
Contact:			





P710116-015

Cofield

Cofield Collection Two-Light Polished Chrome Wall Bracket

Category: Wall Brackets Finish: Polished Chrome (Plated) Construction: Steel Construction

Glass/Shade: Etched White Glass Cylindrical



Width: 22-1/2 in Extends: 5-5/8 in Height: 4-7/8 in

H/CTR: 11-1/4 in (glass facing up)

Etched White Glass Cylindrical

Width: 4 in Height: 8-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall horizontal or vertical	6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.87" W., 0.87" ht., 4.87" depth		Fully dimmable with dimmable bulbs	