



Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P710118-31M Modern Glass Sconce

Modern Glass Sconce Two-Light Matte Black Wall Sconce

**Category:** Wall Sconces  
**Finish:** Matte Black (Painted)  
**Construction:** Steel Construction  
**Glass/Shade:** Etched Glass Square/Rectangular



Width: 12 in  
 Extends: 4 in  
 Height: 7-1/2 in  
 H/CTR: 3-3/4 in

Etched Glass Square/Rectangular  
 Width: 11-1/4 in  
 Height: 6-9/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 10.81" W., 6.68" ht., 0.65" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	Americans With Disabilities Act (ADA) compliant
		Fully dimmable with dimmable bulbs	