

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P710119-009 Silva

Silva Collection Two-Light Brushed Nickel White Linen Shade Wall Sconce

Category: Wall Sconce

Finish: Brushed Nickel (Plated)

Construction: Steel Construction

Glass/Shade: White Linen Fabric Half Cylinder



Width: 7-7/8 in
Extends: 4-7/8 in
Height: 17 in
H/CTR: 8.5 in (glass facing up)

White Linen Fabric Half Cylinder
Width: 7-1/8 in
Height: 17 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.75" W., 7.87" ht., 0.81" depth		Fully dimmable with dimmable bulbs	