

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P710119-31M Silva

Silva Collection Two-Light Matte Black White Linen Shade Wall Sconce

Category: Wall Sconce
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: White Linen Fabric Half Cylinder



Width: 7-7/8 in
 Extends: 4-7/8 in
 Height: 17 in
 H/CTR: 8.5 in (glass facing up)

White Linen Fabric Half Cylinder
 Width: 7-1/8 in
 Height: 17 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.75" W., 7.87" ht., 0.81" depth		Fully dimmable with dimmable bulbs	