

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P710120-31M Arya

Arya Collection Four-Light Matte Black Luxe Wall Bracket

Category: Wall Bracket
Finish: Matte Black (Painted)
Construction: Steel Construction



Width: 20 in (mounted horizontal, does not include bulbs)
 Extends: 2-7/8 in
 Height: 4.5 in
 H/CTR: 2-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Candelabra Base (E12) Socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Fixture can be installed with bulb facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	Americans With Disabilities Act (ADA) compliant
Canopy covers a standard 4" recessed outlet box: 4.5" W., 7" ht., 0.75" depth		Fully dimmable with dimmable bulbs	