

Project: \_\_\_\_\_  
 Fixture Type: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Contact: \_\_\_\_\_



## P710121-31M Rivera

Rivera Collection One-Light Matte Black Luxe Industrial Wall Bracket

**Category:** Wall Brackets  
**Finish:** Matte Black (Painted)  
**Construction:** Steel Housing  
**Glass/Shade:** Clear textured Glass Flat Square/Rectangular

Width: 4-1/2 in  
 Extends: 4-3/4 in  
 Height: 18 in  
 H/CTR: 7-1/2 in

Clear textured Glass Flat Square/Rectangular  
 Width: 3-5/8 in  
 Height: 8-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Candelabra Base (E12) Socket	cULus Damp Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.5" W., 5.5" ht., 0.75" depth		Fully dimmable with dimmable bulbs.	