

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P710122-205 Lusail

Lusail Collection Two-Light Soft Gold Luxe Industrial Wall Bracket

**Category:** Wall Brackets

**Finish:** Soft Gold (Painted), with Foundry Gold accent

**Construction:** Steel Housing



Width: 5-7/8 in  
Extends: 5 in  
Height: 23-1/2 in (mounted vertical)  
H/CTR: 11-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Candelabra Base (E12) Socket	cETLus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5" W., 7" ht., 0.75" depth		Fully dimmable with dimmable bulbs.	