

Project:			
Fixture Type:			
Location:			





P710123-204

Laurel

Contact:

Laurel Collection Four-Light Gold Ombre Transitional Wall Bracket

Category: Wall Brackets

Finish: Gold Ombre (Hand Painted) **Construction:** Steel Housing

Width: 9 in Extends: 4-3/8 in

Height: 24-1/2 in (Mounted Vertical)

H/CTR: 12-1/4 in

		1 11	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Candelabra Base (E12) Socket	cETLus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.75" W.,		LED: 12.5-watt MAX per socket	
0.75" ht., 4.75" depth		Fully dimmable with dimmable bulbs.	