PROGRESS LIGHTING DESIGN**+SERIES**™



Project:

Fixture Type:

Location:

Contact:

P710124-204 Loretta

Loretta Collection Four-Light Gold Ombre Transitional Wall Sconce

Category: Wall Sconces Finish: Gold Ombre (Hand Painted) Construction: Steel Housing Glass/Shade: Clear Glass Round



Width: 24 in Extends: 4-7/8 in Height: 12-3/4 in (Mounted Horizontal) H/CTR: 12 in

Clear Glass Round Width: 6-11/16 in Height: 1-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Candelabra Base (E12) Socket	cETLus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 40-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.12" W.,		LED: 10-watt MAX per socket	
0.75" ht., 5.12" depth		Fully dimmable with dimmable bulbs.	