

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P710125-176 Chevall

Chevall Collection Two-Light Gilded Silver Modern Organic Wall Sconce

Category: Wall Sconces
Finish: Gilded Silver (Hand Painted)
Construction: Steel Housing
Glass/Shade: Clear Pressed Glass Flat Square/Rectangular



Width: 7 in
 Extends: 4-1/2 in
 Height: 15 in
 H/CTR: 8-1/4 in

Clear Pressed Glass Flat Square/Rectangular
 Width: 6-11/16 in
 Height: 15 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Candelabra Base (E12) Socket	cETLus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.5" W., 0.81" ht., 5.5" depth		Fully dimmable with dimmable bulbs.	