## PROGRESS LIGHTING DESIGN**+SERIES**™

Project:			
Fixture Type:			_
Location:			_
Contact:			

## **P710125-204** Chevall

Chevall Collection Two-Light Gold Ombre Modern Organic Wall Sconce

Category: Wall Sconces Finish: Gold Ombre (Hand Painted) Construction: Steel Housing Glass/Shade: Clear Pressed Glass Flat Square/Rectangular



Width: 7 in Extends: 4-1/2 in Height: 15 in H/CTR: 8-1/4 in

Clear Pressed Glass Flat Square/Rectangular Width: 6-11/16 in Height: 15 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Candelabra Base (E12) Socket	cETLus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.5" W., 0.81"		LED: 12.5-watt MAX per socket	
ht., 5.5" depth		Fully dimmable with dimmable bulbs.	