

Project:			
Fixture Type:			
Location:			





P710126-009

Boundary

Contact:

Boundary Collection Two-Light Brushed Nickel Grey Washed Oak Modern Wall Bracket

Category: Wall Brackets

Finish: Brushed Nickel (Plated) with Grey Washed Oak accent

Construction: Steel Housing, Solid Wood accent

Width: 24 in Extends: 5-1/4 in Height: 5-1/2 in

H/CTR: 2-3/4 in (mounted horizontal)

	, = = 3/4 (
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION	
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cETLus Damp Location Listed	
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty	
Fixture can be installed with glass facing up or down		LED: 12.5-watt MAX per socket		
		Fully dimmable with dimmable		
Canopy covers a standard 4" recessed outlet box: 7.06" W., 5.5" ht., 0.81" depth		bulbs.		