

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____



P710126-31M Boundary

Boundary Collection Two-Light Matte Black Roasted Chicory Modern Wall Bracket

Category: Wall Brackets
Finish: Matte Black (Hand Painted) with Roasted Chicory accent
Construction: Steel Housing, Solid Wood accent

Width: 24 in
 Extends: 5-1/4 in
 Height: 5-1/2 in
 H/CTR: 2-3/4 in (mounted horizontal)

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cETLus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 7.06" W., 5.5" ht., 0.81" depth			