

Project: \_\_\_\_\_  
 Fixture Type: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Contact: \_\_\_\_\_

## P710127-205 Pinellas

Pinellas Collection 22.5 in. One-Light Soft Gold Contemporary Wall Bracket

**Category:** Wall Brackets  
**Finish:** Soft Gold (Painted)  
**Construction:** Steel Housing  
**Glass/Shade:** Gloss Finish Opal Glass Cone



Width: 5-1/8 in  
 Extends: 5-3/4 in  
 Height: 22-1/2 in  
 H/CTR: 9 in

Gloss Finish Opal Glass Cone  
 Width: 4-1/2 in  
 Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Candelabra Base (E12) Socket	cETLus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth		Fully dimmable with dimmable bulbs.	