

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____



P710128-204 Loretta

Loretta Collection One-Light Gold Ombre Transitional Wall Bracket

Category: Wall Brackets
Finish: Gold Ombre (Hand Painted)
Construction: Steel Housing
Glass/Shade: Clear Glass Round

Width: 6-5/8 in
 Extends: 4-7/8 in
 Height: 9-1/4 in
 H/CTR: 6-3/8 in

Clear Glass Round
 Width: 6-11/16 in
 Height: 1-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Candelabra Base (E12) Socket	cETLus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth		Fully dimmable with dimmable bulbs.	