

Project:

Fixture Type:

Location:

Contact:

## P710130-009

## Haas

Haas Collection Four Light Brushed Nickel Mid-Century Modern Wall Bracket

Category: Wall Brackets Finish: Brushed Nickel (Plated) Construction: Steel Housing

Glass/Shade: Etched Opal Glass Round



Width: 5-7/8 in Extends: 7-1/8 in Height: 24 in

H/CTR: 12 in (mounted vertical)

Etched Opal Glass Round

Width: 6 in Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Candelabra Base (E12) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.12" W.,		LED: 12.5-watt MAX per socket	
0.87" ht., 5.12" depth		Dimmable to 10% brightness (See Dimming Notes)	