

Project:

Fixture Type:

Location:

Contact:

## P710131-009

## Cornett

Cornett Collection One-Light Brushed Nickel Contemporary Wall Sconce

Category: Wall Brackets Finish: Brushed Nickel (Plated) Construction: Steel Housing

Glass/Shade: Brushed Nickel, Painted White Inside Metal Cone



Width: 4-1/2 in Extends: 20 in Height: 19 in H/CTR: 9-9/16 in

Brushed Nickel, Painted White Inside Metal Cone

Width: 2-1/2 in Height: 3-13/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC Switch Type: On/Off	Lamp Type 15 W max LED	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.5" W., 7.5" ht., 1" depth		Fully dimmable with dimmable bulbs.	

