

Project:
Fixture Type:

Location:
Contact:

## **P710131-191** Cornett

Cornett Collection One-Light Brushed Gold Contemporary Wall Sconce

Category: Wall Brackets Finish: Brushed Gold (Plated) Construction: Steel Housing

Glass/Shade: Brushed Gold, Painted White Inside Metal Cone



Width: 4-1/2 in Extends: 20 in Height: 19 in H/CTR: 9-9/16 in

Brushed Gold, Painted White Inside Metal Cone

Width: 2-1/2 in Height: 3-13/16 in

	Height: 3-13/16 in		
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC Switch Type: On/Off	Lamp Type 15 W max LED	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.5" W., 7.5" ht., 1" depth	owner Type: Ony on	Fully dimmable with dimmable bulbs.	

On/Off touch switch