

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P710136-205 Seville

Wall Sconce

**Category:** Wall Sconce

**Finish:** Soft Gold (Painted)

**Construction:** Steel Construction

**Glass/Shade:** Clear w/ Vertical Flutes Glass Flat Round



Width: 6 in  
Extends: 3 in  
Height: 18 in  
H/CTR: 9 in (glass facing up)

Clear w/ Vertical Flutes Glass Flat Round  
Width: 7-9/16 in  
Height: 18 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Candelabra Base (E12) Socket	cETLus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	Americans With Disabilities Act (ADA) compliant
Canopy covers a standard 4" recessed outlet box: 6" W., 18" ht., 0.75" depth		Fully dimmable with dimmable bulbs	