

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P710138-31M

### Tosca

Wall Bracket

**Category:** Wall Bracket

**Finish:** Matte Black (Painted)

**Construction:** Steel Construction

**Glass/Shade:** Faux Alabaster Glass Cone



Width: 4-1/2 in  
Extends: 6 in  
Height: 10 in  
H/CTR: 5 in (glass facing up)

Faux Alabaster Glass Cone  
Width: 3-1/2 in  
Height: 5-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Candelabra Base (E12) Socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 10" ht., 0.81" depth		Fully dimmable with dimmable bulbs	