

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____



Incandescent

P7156-81

Archives

With Archives' pendants and wall sconce, carefully crafted details and special accents achieve a vintage electric feel. One-light adjustable swivel wall sconce with brushed nickel accents.

- Carefully crafted details.
- Vintage electric feel.
- Antique Nickel with Brushed Nickel accents.

Category: Wall Sconce

Finish: Antique Nickel (Plated)

Construction: Steel construction

Glass/Shade: PMS Matte Cool Grey #9 metal shade

Width: 9"
Height: 7"
Depth: 10"
H/CTR: 2-3/8"

Shade
Width: 9-1/16"
Height: 1-7/8"

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|---|---|---|---|
| Wall mounted Mounting strap for outlet box included Back plate covers a standard 4" octagonal recessed outlet box 4.75" W., 1" depth | Pre-wired 6" of wire supplied 120 V | Quantity: One 100w max. Medium Base E26 base porcelain socket | UL-CUL Dry location listed 1 year warranty |