

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____



Linear fluorescent

P7229-09EB

Linear Fluorescent Bath

White acrylic diffuser with contemporary metal end caps using a 120V NPF electronic ballast. This fixture uses long-life electronic ballast for superior performance and reliability.

- Brushed Nickel finish.
- White acrylic diffuser.
- Contemporary metal end caps.
- Superior performance and reliability.

Category: Bath & Vanity

Finish: Brushed Nickel (Plated)

Construction: Steel constructionSteel construction

Glass/Shade: White acrylic diffuser

Width: 49-1/4"
Height: 4-1/2"
Depth: 4-1/2"
H/CTR: 2-1/4" (mounted horizontally)

Glass:
Length: 48"
Height: 3-3/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall horizontal or vertical mounted Backplate 22.75" W., 2.625" ht.	Pre-wired 6" of wire supplied 120 V	Quantity: Two 32w max. F32T8 Bi-pin twist-in base lamp holders	UL-CUL Damp location listed 1 year warranty