

Flush Mount Linear LED

 Flush-Mount mounted • Damp location listed **PROGRESS LED**


P7258-17430K9


Description:

LED Linear Cloud features an LED light source, offering both form and function with energy- and cost-savings benefits. The LED Linear Cloud can be used in kitchens, basements, garages and many other utility areas. It has a white contoured shallow acrylic cloud lens with Urban Bronze finish end caps. The LED Linear Cloud is a ceiling mount fixture that delivers 3,676 lumens, is 90 CRI and with 3000K color temperature. Acrylic diffuser gives even light distribution. ENERGY STAR certified, Title 24 compliant, Damp location listed. Flicker-free dimming to 10 percent brightness with most Forward Phase Triac dimmers.

Specifications:

- Urban Bronze (-174) (plated)
- Steel construction
- White acrylic diffuser
- LED Linear Cloud
- Features an LED light source, offering both form and function with energy- and cost-savings benefits
- The LED Linear Cloud can be used in kitchens, basements, garages and many other utility areas
- White contoured shallow acrylic cloud lens
- The LED Linear Cloud is a ceiling mount fixture
- 53W LED module offers 71 lumens per watt
- 3,676 lumens, 90 CRI and 3000K color temperature
- Acrylic diffuser for even light distribution
- Measures 4 1/2" H x 11 3/4" W x 48-5/16"L
- Title 24 compliant
- Damp location listed
- Mounting for outlet box included
- Canopy covers standard 4 hexagonal outlet box
- Steel construction
- Flicker-free dimming to 10% brightness with most Forward Phase (Triac) dimmers
- 5-year warranty
- Dimmable to 10% brightness (See Dimming Notes)
- Mounting housing for outlet box included
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

Images:



Dimensions:

Width: 11-13/16"

Height: 4-1/2"

Performance:

Number of Modules	1
Input Power	52w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	3676/71 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	54,000 (L70/TM-21)
Min. Start Temp	-30 °C
Warranty	5 year warranty
Labels	cETLus Damp location listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016

P7258-17430K9

Dimming Notes:

P7258 is designed to be compatible with many Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron DVCL-153P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.