

LED Wraps

Wall or ceiling Mounted • Damp Location Listed PROGRESS LED



Description:

The Wrap and Strip Collection's Two-Foot LED Wrap Light features a crisp white acrylic diffuser shaped into an elegant elongated tubular silhouette. The light fixture is complemented by white end caps and a white metal chassis. The wrap light can be mounted on a wall or ceiling to meet your unique design needs.


Specifications:

- White polycarbonate diffuser
- Features a crisp white acrylic diffuser shaped into an elongated tubular silhouette.
- Complemented by white end caps and a white metal chassis.
- Can be mounted on a wall or ceiling to meet your unique design needs.
- Ideal for kitchens, laundry rooms, garage utility areas, and work spaces.
- Damp location listed.
- Measures 47.346-inch width by 2.992-inch height.
- Uses one integrated LED bulb (40w).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.
- Dimmable to 10% brightness (See Dimming Notes)
- Mounting backplate for outlet box included
- 6 in of wire supplied

Performance:

Number of Modules	1
Input Power	40 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	3,400/85 (LM-79)CRI 90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016

P730012-030-30



Dimensions:

Width: 47-3/8 in
 Height: 6-3/16 in
 Depth: 2-15/16 in

Dimming Notes:

P730012-030-30 is designed to be compatible with many ELV controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P730012-030-30