

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Compact fluorescent

P7339-30EBWB

Bulkheads

Two-Light 10-5/8" Non-Metallic Oval Wall or Ceiling Mount Bulkhead. Virtually maintenance free fixtures that can install on ceilings or walls. Classic white details and trim, Corrosion and impact shatter resistant. UV stabilized. White finish.

- Colors will not fade and parts will not corrode.
- Mount on walls or ceilings.
- Polycarbonate light for indoor and outdoor areas.

Category: Outdoor

Finish: White (White)

Construction: Polycarbonate Construction

Glass/Shade: White polycarbonate lens



Width: 10-5/8"
Height: 6-3/4"
Depth: 4-1/2"
H/CTR: 5-3/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall or ceiling mounted Mounting strap for outlet box included Complies with "Americans with Disabilities Act" - ADA Back plate covers a standard 4" octagonal recessed outlet box 10.5625" W., 6" ht., 1.304" depth	Pre-wired 6" of wire supplied 120V NPF electronic 120 V	Quantity: Two 13w max. 4-pin, triple tube compact fluorescent (included) GX24q-1 base plastic sockets G24q-2 base	cCSAus Wet location listed 1 year warranty