

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Compact fluorescent

P7372-30STRWB

Hard-Nox

Two-light flush mount with white acrylic diffuser mounts to baked enamel ceiling pan. Twist on installation with a single locking thumb screw. UL approved for damp locations. Rapid start 120V HPF ballast. Ceiling or wall mount. ADA compliant when wall mounted. Lamps included.

- Two-light flush mount.
- White acrylic diffuser mounts to baked enamel ceiling pan.
- Twist on installation with a single locking thumb screw.
- Ceiling or wall mount.
- UL approved for damp locations.
- Ceiling or wall mount.

Category: Outdoor

Finish: White (Baked Enamel)

Construction: Steel Construction

Glass/Shade: White acrylic cloud diffuser



Diameter: 13-7/8"

Height: 3-1/8"

Glass

Width: 13-7/8"

Height: 2-3/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall or ceiling mounted Mounting screws for outlet box included Complies with "Americans with Disabilities Act" - ADA Ceiling pan covers a standard 4" octagonal recessed outlet box	Pre-wired 6" of wire supplied 120 V	Quantity: Two 13w max. 4-pin, quad compact fluorescent(included) G24q-1 base sockets	UL-CUL Damp location listed 1 year warranty