

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Compact fluorescent

P7375-30STRWB

Hard-Nox

One-light flush mount with white acrylic diffuser mounts to baked enamel ceiling pan. Twist on installation with a single locking thumb screw. UL approved for damp locations. Rapid start 120V HPF ballast. Ceiling or wall mount. ADA compliant when wall mounted. Lamps included.

- One-light flush mount.
- White acrylic diffuser mounts to baked enamel ceiling pan.
- Twist on installation with a single locking thumb screw.
- Ceiling or wall mount.
- UL approved for damp locations.
- Ceiling or wall mount.

Category: Outdoor

Finish: White (baked enamel)

Construction: Steel Construction

Glass/Shade: White acrylic cloud diffuser



Diameter: 9"
Height: 3-3/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Wall or ceiling mounted</p> <p>Mounting strap for outlet box included</p> <p>Complies with "Americans with Disabilities Act" - ADA</p> <p>Unit covers a standard 4" octagonal recessed outlet box</p> <p>10.125" W., 0.25" ht., 10.125" depth</p>	<p>Pre-wired</p> <p>6" of wire supplied</p> <p>120V NPF electronic 120 V</p>	<p>Quantity:</p> <p>One 13w max. 4-pin, quad compact fluorescent (included)</p> <p>G24q-1 base socket</p>	<p>UL-CUL Damp location listed</p> <p>1 year warranty</p>