

Project:

Fixture Type:

Location:

Contact:

# Intrinsic

Recessed housing Mounted • Wet Location Listed PROGRESS LED



### **Description:**

Intrinsic Collection 1-Light Satin White Modern Recessed LED Downlight

## **Specifications:**

- Pairs With: Use with P86, P186, P851-ICAT, P1851-ICAT, P1841-ICAT, P871-LED-001, and P1871-LED-001 Progress Lighting Housings.
- · Dimmable to 10% brightness (See Dimming Notes)
- 6 in of wire supplied

#### **Performance:**

Number of Modules	1
nput Power	8 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	757/97 (LM-79)
ССТ	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Wet Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016

# P800002-028-30



#### **Dimensions:**

Length: 7-3/8 in Diameter: 7-3/8 in Height: 2.36 in