

Intrinsic

Recessed housing Mounted • Damp Location Listed PROGRESS LED



Description:

Intrinsic 5" / 6" 5-CCT LED Eyeball (P851-ICAT/P1851-ICAT/P1841-ICAT/P87-AT/P87-ATQC/P187-TG/P86-TG/P186-TG/P821-FBFC/P821-FB/P871-LED/P1871-LED)

Specifications:

- Dimmable to 10% brightness (See Dimming Notes)
- 6 in of wire supplied

Performance:

Number of Modules	1
Input Power	8 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	750/93 (LM-79)
CCT	2700 K
	3000 K
	3500 K
	4000 K
	5000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	ENERGY STAR® qualified
	Meets California Title 20

P800018-028-CS



Dimensions:

Length: 7-11/16 in
 Diameter: 7-11/16 in
 Height: 3-15/16 in



The adjustable light source can be aimed allowing the trim to be used as a standard downlight, accent light, wall wash or sloped ceiling light.

P800018-028-CS

Dimming Notes:

P800018-028-CS is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Eaton AAL06

Eaton SAL06P

IDevices IDEV009

Leviton_Trimatron 6681

Leviton IPI06-1LZ

Leviton 6672

Leviton 6674

Lutron NTEVL-300

Lutron DVELV-300P

Lutron Caseta Wireless

Lutron AYCL-153P

Lutron SCL-153P

Lutron TGCL-153-PH-WH

Lutron MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.