

Project:

Fixture Type:

Location:

Contact:

4IN RECESSED

Ceiling in recessed housing Mounted • Damp Location Listed

Description:

4" Baffle Trim

Performance:

Input Power	50 W
Input Voltage	120 VAC
Warranty	1-year Limited Warranty
Labels	cULus Damp Location Listed

P804000-031



Dimensions:

Diameter: 4-15/16 in Height: 2-3/16 in

Compatible housing and lamp information:

	NON IC		IC	
HOUSING	LAMP SHAPE	MAX WATTS	LAMP SHAPE	MAX WATTS
P804N-N-MD-ICAT	PAR20	50W	PAR20	50W
	R20	50W	R20	50W
P804N-N-MD-AT	PAR20	50W		
	R20	50W		
	A19	40W		
P804N-R-MD-AT	PAR20	50W		
	R20	50W		
	A19	40W		