

Project:		
Fixture Type:		
Location:		

4IN RECESSED

Ceiling in recessed housing Mounted • Damp Location Listed

Contact:

Description:

4" Open Trim

Performance:

Input Power	50 W
Input Voltage	120 VAC
Warranty	1-year Limited Warranty
Labels	cULus Damp Location Listed





Dimensions:

Diameter: 5 in Height: 3-3/8 in

Compatible housing and lamp information:

	NON IC		IC	
HOUSING	LAMP SHAPE	MAX WATTS	LAMP SHAPE	MAX WATTS
P804N-N-MD-ICAT	PAR20	50W	PAR20	50W
	R20	50W	R20	50W
	A19	40W	A19	40W
P804N-N-MD-AT	PAR20	50W		
	R20	50W		
	A19	40W		
P804N-R-MD-AT	PAR20	50W		
	R20	50W		
	A19	40W		