

Project:

Fixture Type:

Location:

Contact:

6IN RECESSED

Ceiling in recessed housing Mounted • Damp Location Listed

Description:

6" Recessed Trim

Performance:

Input Power	90 W
Input Voltage	120 VAC
Warranty	1-year Limited Warranty
Labels	cULus Damp Location Listed

P806001-031



Dimensions:

Diameter: 7-1/4 in Height: 4-7/8 in

Compatible housing and lamp information:

	NON IC		IC	
HOUSING	LAMP SHAPE	MAX WATTS	LAMP SHAPE	MAX WATTS
P806N-N-MD-ICAT	PAR38	90W	PAR38	90W
	BR30	65W	BR30	65W
	R30	75W	R30	75W
	PAR30	50W	PAR30	50W
	PAR30L	75W	PAR30L	75W
P806N-R-MD-ICAT	R40	85W	R40	85W
	PAR38	90W	PAR38	90W
	R30	75W	R30	75W
	PAR30	75W	PAR30	75W