

Project:		
Fixture Type:		
Location:		

## **6IN RECESSED**

Ceiling in recessed housing Mounted • Damp Location Listed

Contact:

### **Description:**

6" Splay Baffle Trim

# Performance:

Input Power	90 W
Input Voltage	120 VAC
Warranty	1-year Limited Warranty
Labels	cULus Damp Location Listed





#### **Dimensions:**

Diameter: 8 in Height: 5-1/8 in

### Compatible housing and lamp information:

	NON IC		ıc	
HOUSING	LAMP SHAPE	MAX WATTS	LAMP SHAPE	MAX WATTS
P806N-N-MD-ICAT	BR40	90W	BR40	90W
	PAR38	90W	PAR38	90W
	BR30	65W	BR30	65W
	R30	75W	R30	75W
	PAR30	75W	PAR30	75W
	PAR30L	75W	PAR30L	75W
P806N-R-MD-ICAT	R40	85W	R40	85W
	PAR38	90W	PAR38	90W
	R30	75W	R30	75W
	PAR30	75W	PAR30	75W