

Fixture Typ	oe:			
-------------	-----	--	--	--

Contact:

6IN RECESSED

Ceiling in recessed housing Mounted • Wet Location Listed

Description:

6" Shower Trim

P806004-028

Performance:

Input Power 40 W
Input Voltage 120 VAC
Warranty 1-year Limited Warranty
Labels cULus Wet Location Listed



Dimensions:

Diameter: 8-1/4 in Height: 1-1/4 in

Clear Glass Round Width: 5-1/8 in Height: 0-3/8 in

Compatible housing and lamp information:

	NON IC		IC		
HOUSING	LAMP SHAPE	MAX WATTS	LAMP SHAPE	MAX WATTS	
P806N-N-MD-ICAT	A19	40W	A19	40W	
P806N-R-MD-ICAT	A19	40W	A19	40W	
P806S-N-MD-ICAT	A19SBLED	10W	A19SBLED	10W	
P806S-R-MD-ICAT	A19SBLED	10W	A19SBLED	10W	
P806A-N-MD-ICAT	A19	40W			
P806A-N-MD-AT	A19	60W			
P806A-R-MD-AT	A19	60W			