

Project: Fixture Type:

Location:

Contact:

6IN RECESSED

Ceiling in recessed housing Mounted • Wet Location Listed

Description:

6" Drop Lensed Shower Trim

Performance:

Input Power	40 W
Input Voltage	120 VAC
Warranty	1-year Limited Warranty
Labels	cULus Wet Location Listed



P806005-028

Dimensions:

Diameter: 7.5 in Height: 2.5 in

Clear Glass Round Width: 5-3/16 in Height: 1-1/8 in

Compatible housing and lamp information:

	NON IC		IC	
HOUSING	LAMP SHAPE	MAX WATTS	LAMP SHAPE	MAX WATTS
P806N-N-MD-ICAT	A19	40W	A19	40W
P806N-R-MD-ICAT	A19	40W	A19	40W
P806S-N-MD-ICAT	A19SBLED	10W	A19SBLED	10W
P806S-R-MD-ICAT	A19SBLED	10W	A19SBLED	10W
P806A-N-MD-ICAT	A19	40W		
P806A-N-MD-AT	A19	60W		
P806A-R-MD-AT	A19	60W		