

Project:

Fixture Type:

Location:

Contact:

6IN RECESSED SHALLOW Ceiling in recessed housing Mounted • Damp Location Listed

Description:

6" Baffle Trim

Performance:

Input Power	50 W
Input Voltage	120 VAC
Warranty	1-year Limited Warranty
Labels	cULus Damp Location Listed

P806006-031



Dimensions:

Diameter: 7-5/16 in Height: 3-3/4 in

Compatible housing and lamp information:

	NON IC		IC	
HOUSING	LAMP SHAPE	MAX WATTS	LAMP SHAPE	MAX WATTS
P806S-N-MD-ICAT	BR30	50W	BR30	50W
	R30	50W	R30	50W
	PAR30	50W	PAR30	50W
P806S-R-MD-ICAT	BR30	50W	BR30	50W
	R30	50W	R30	50W
	PAR30	50W	PAR30	50W