

Fixture Type	e.				
--------------	----	--	--	--	--

# 6IN RECESSED SHALLOW Ceiling in recessed housing Mounted • Damp Location Listed

#### **Description:**

6" Recessed Trim

# P806007-028

#### **Performance:**

Input Power	50 W
Input Voltage	120 VAC
Warranty	1-year Limited Warranty
Labels	cULus Damp Location Listed



### **Dimensions:**

Contact:

Diameter: 7-5/16 in Height: 3-3/4 in

## Compatible housing and lamp information:

	NON IC		ıc	
HOUSING	LAMP SHAPE	MAX WATTS	LAMP SHAPE	MAX WATTS
P806S-N-MD-ICAT	BR30	50W	BR30	50W
	R30	50W	R30	50W
	PAR30	50W	PAR30	50W
P806S-R-MD-ICAT	BR30	50W	BR30	50W
	R30	50W	R30	50W
	PAR30	50W	PAR30	50W