

6IN RECESSED SLOPE

Ceiling in recessed housing Mounted • Damp Location Listed

Description:

6" Slope Baffle Trim

Performance:

Input Power	75 W
Input Voltage	120 VAC
Warranty	1-year Limited Warranty
Labels	cULus Damp Location Listed

P806008-020



Dimensions:

Diameter: 8-1/8 in
Height: 3-5/8 in

Compatible housing and lamp information:

HOUSING	NON IC		IC	
	LAMP SHAPE	MAX WATTS	LAMP SHAPE	MAX WATTS
P806A-N-MD-ICAT	BR30	75W	BR30	75W
	R30	75W	R30	75W
	PAR30L	75W	PAR30L	75W
P806A-N-MD-AT	BR30	100W		
	R30	100W		
	PAR30L	75W		
P806A-R-MD-AT	BR30	100W		
	R30	100W		
	PAR30L	75W		